



Parata™ Perl™

Pouch Inspector

Complete your pouch packaging workflow with automated inspection that **alleviates time-consuming manual** verification while helping to increase accountability and accuracy. Parata™ Perl™ gives the pharmacy team time to do more.



Parata™

Make your workflow work for you.

Parata™ Perl™ pouch inspector keeps up with your growing business with scalable add-on capabilities, high-definition inspection technology, and compatibility with both PASS™ and ATP™ pouches.



Highlighted Features:

- Parata™ Perl™ inspects up to five pouches per second.
- Increase efficiency with two powerful, high-definition cameras that identify the contents of each pouch.
- The intelligent, web-based inspection application—accessible from any computer or mobile device in your network—identifies existing drugs and learns new ones quickly.

Parameters

Specifications

Included with your purchase	<ul style="list-style-type: none">– Parata™ Perl™ Pouch Inspector– Parata™ Perl™ Pouch Inspector web application licenses (2)– Keyboard with integrated track pad (1)– Correction camera (1)	<ul style="list-style-type: none">– Barcode scanner (1)– Bins (3)– Four Spools and one winder based on configuration choice
Spool capacity	19" in. spool holds 1,200 pouches. 27" in. spool holds 2,000 pouches	
Optional Components	<ul style="list-style-type: none">– Perl workflow table (1) 45¼" (W) x 27½" (D) x 35½" (H)– Additional web application user licenses– Parata™ Perl™ Cut and Roll pouch inspector	
Cut & Roll Capacity	<ul style="list-style-type: none">– 350 pouches for unit dose 55mm dispensing– 275 pouches for a typical 75mm multi-dose pharmacy– 200 pouches for fuller multi-dose 95mm dispensing	
Cut & Roll Inspection Speed	– Up to 2.5 pouches per second	
Cut & Roll Function	– Cuts and tapes by patient, facility, or hour of administration	
Power Requirements	120VAC, 15A, 60Hz, single phase, standard outlet	
Network Requirements	Ethernet RJ-45 (Cat VI)	

[parata.com](https://www.parata.com)